

PCB Plain Copper Busbar



CARACTERÍSTICAS

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

Material: Copper



ESPECIFICAÇÕES

Table 1/2


Número de catálogo	Número do artigo	Largura (W)	Espessura (T)	Length (L)	Peso unitário
PCB-1M-12X4	550780	12 mm	4 mm	990mm	0.43 kg
PCB-2M-100X10	549750	100 mm	10 mm	2000mm	17.8 kg
PCB-2M-100X5	549640	100 mm	5 mm	2000mm	8.9 kg
PCB-2M-120X10	549760	120 mm	10 mm	2000mm	21.4 kg
PCB-2M-12X4	550790	12 mm	4 mm	1985mm	0.85 kg
PCB-2M-12X5	550770	12 mm	5 mm	1985mm	1.06 kg
PCB-2M-25X5	549600	25 mm	5 mm	2000mm	2.2 kg
PCB-2M-30X10	549700	30 mm	10 mm	2000mm	5.5 kg
PCB-2M-40X10	549710	40 mm	10 mm	2000mm	7.1 kg
PCB-2M-50X10	549720	50 mm	10 mm	2000mm	8.9 kg
PCB-2M-50X5	549610	50 mm	5 mm	2000mm	4.5 kg
PCB-2M-60X10	549730	60 mm	10 mm	2000mm	10.7 kg
PCB-2M-63X5	549620	63 mm	5 mm	2000mm	5.6 kg

Número de catálogo	Número do artigo	Largura (W)	Espessura (T)	Length (L)	Peso unitário
PCB-2M-80X10	549740	80 mm	10 mm	2000mm	14.2 kg
PCB-2M-80X5	549630	80 mm	5 mm	2000mm	7.1 kg
PCB-4M-100X10	550930	100 mm	10 mm	4000mm	35.6 kg
PCB-4M-100X5	550670	100 mm	5 mm	4000mm	17.8 kg
PCB-4M-120X10	550940	120 mm	10 mm	4000mm	42.8 kg
PCB-4M-160X10	550950	160 mm	10 mm	4000mm	57 kg
PCB-4M-20X5	550600	20 mm	5 mm	4000mm	3.56 kg

Table 2/2

Número de catálogo	Número do artigo	Largura (W)	Espessura (T)	Length (L)	Peso unitário
PCB-4M-25X5	550610	25 mm	5 mm	4000mm	4.45 kg
PCB-4M-30X10	550970	30 mm	10 mm	4000mm	10.69 kg
PCB-4M-30X5	550620	30 mm	5 mm	4000mm	5.34 kg
PCB-4M-40X10	550980	40 mm	10 mm	4000mm	14.25 kg
PCB-4M-40X5	550630	40 mm	5 mm	4000mm	7.12 kg
PCB-4M-50X10	550900	50 mm	10 mm	4000mm	17.8 kg
PCB-4M-50X5	550640	50 mm	5 mm	4000mm	8.9 kg
PCB-4M-60X10	550910	60 mm	10 mm	4000mm	21.35 kg
PCB-4M-60X5	550650	60 mm	5 mm	4000mm	10.68 kg
PCB-4M-80X10	550920	80 mm	10 mm	4000mm	28.5 kg
PCB-4M-80X5	550660	80 mm	5 mm	4000mm	14.24 kg

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.