


nVent CADDY Telescoping Screw Gun Box Bracket, First Means



The nVent CADDY Telescoping Screw Gun Box Bracket, First Means is a simple and intuitive support for mounting electrical boxes within stud wall applications. This solution delivers both traditional and retrofit mounting, which allows the bracket to bend for multiple depths and mount from both the front and back of the stud—making it ideal for when drywall has already been installed. As the first means of support, conduit can be run directly to the electrical box while ensuring a smooth, flat drywall finish with side-mount installations. The notched and clearly marked bend points make installation safe, fast and easy.

CARACTERISTICI

Designed for both single and multiple box mounting

Unique single-component break-apart design

Stamped inch markings and pilot holes accelerate precise box conduit mounting

Pilot holes allow for easy access with a screwdriver

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly



SPECIFICAȚII

Număr de catalog	Article Number	Material	Finish	Stud Spacing	Box Depth
TSGB1624	187199	Oțel	Pregalvanized	400 - 635 mm	38mm, 54mm, 63.5mm

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

