

PXI-Express System, 4 U, 8 slots, Gen 3

NÚMERO DE CATÁLOGO

14579-030

Desktop PXI Express Chassis for one PXI Express System Controller with up to 16 HP and 7 PXI or PXI Express Boards with 4 HP Width.

CARACTERÍSTICAS

PXI Express Desktop Chassis, 4 U, 44 HP

1 PXIe System Slot and 7 Hybrid Slots

Ultra-high performance Gen 3 PCIe switching with a default four-link (4x4) System Slot

Powerful cooling concept with low fan noise, 50 W per slot @ 15K temperature increase

Air flow from bottom to rear with temperature controlled fans; Integrated Chassis Monitoring Modul (CMM)

Wide range AC input with mains switch on the rear side, power push button on the front (top)

Rear panel external 10 MHz clock inputs/outputs



CARATERÍSTICAS DO PRODUTO

Product Type: System

Number of Slots: 8

Tipo: Desktop

Backplane Type: PXI Express, 4 Link Configuration

Data Transfer: PCIe Gen3

Power per Slot: 50W

Tensão de entrada AC: 100 – 240V

Airflow Direction: Bottom to Rear

Rack Height: 4U

Power Supply Type: Open Frame

Power Supply Included: Sim

Rear I/O: Não

Em conformidade com: PXISA PXI-5 R1.1

PXI Express Timing Slot Quantity: 0

Profundidade: 315mm

Net Weight: 8.1kg

Quantidade por embalagem: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALHES ADICIONAIS DO PRODUTO

System in accordance with IEC 60297--3--101, --102, --103; IEEE 1101.1, 1101.10/11); Backplane, conforms to PICMG rev. 3.0 and PXI-5.

Modified systems available on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.