

Hol-Sealers Hole Seal

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hol-Sealers hole seals . Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick. Maintains enclosures Type rating 3R, 4, 4X (Stainless Steel version only) 12, and 13 when installed in an nVent HOFFMAN enclosure.



STANDARDE INDUSTRIALE

UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 (MS)

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 (SS)

Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 12, 13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66

CARACTERISTICI

Se furnizează garnitura rezistentă la ulei

Available in multiple colors and sizes

Steel model has plated stud (10-32x5/8) and wing nut

Stainless steel model has 300 series stainless steel stud (10-24x5/8) and wing nut

SPECIFICAȚII

Table 1/2

Număr de catalog	Material	Finish	Color	Color Code	Thickness	Hole Diameter
AS050	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	22mm max
AS050SS	Stainless Steel 304	Polished			1.5mm	22mm max
AS050LG	Oțel Zincat	Vopsit Pulbere	Light Gray	RAL 7035	1.5mm	22mm max

Număr de catalog	Material	Finish	Color	Color Code	Thickness	Hole Diameter
AS056CB	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	14mm max
AS056M	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	14mm max
AS056MFB	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	14mm max
AS056MLG	Oțel Zincat	Vopsit Pulbere	Light Gray	RAL 7035	1.5mm	14mm max
AS056MSS	Stainless Steel 304	Polished			1.5mm	14mm max
AS075	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	27mm max
AS075LG	Oțel Zincat	Vopsit Pulbere	Light Gray	RAL 7035	1.5mm	27mm max
AS075SS	Stainless Steel 304	Polished			1.5mm	27mm max
AS100	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	35mm
AS100LG	Oțel Zincat	Vopsit Pulbere	Light Gray	RAL 7035	1.5mm	35mm
AS100SS	Stainless Steel 304	Polished			1.5mm	35mm
AS125	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	43mm max
AS125LG	Oțel Zincat	Vopsit Pulbere	Light Gray	RAL 7035	1.5mm	43mm max
AS125SS	Stainless Steel 304	Polished			1.5mm	43mm max
AS150	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	51mm max
AS150LG	Oțel Zincat	Vopsit Pulbere	Light Gray	RAL 7035	1.5mm	51mm max
AS150SS	Stainless Steel 304	Polished			1.5mm	51mm max

Table 2/2

Număr de catalog	Material	Finish	Color	Color Code	Thickness	Hole Diameter
AS200	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	64mm max
AS200LG	Oțel Zincat	Vopsit Pulbere	Light Gray	RAL 7035	1.5mm	64mm max
AS200SS	Stainless Steel 304	Polished			1.5mm	64mm max
AS250	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	76mm max
AS250SS	Stainless Steel 304	Polished			1.5mm	76mm max
AS300	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	92mm max
AS300SS	Stainless Steel 304	Polished			1.5mm	92mm max
AS350	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	105mm max
AS350SS	Stainless Steel 304	Polished			1.5mm	105mm max
AS400	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	117mm max
AS400SS	Stainless Steel 304	Polished			1.5mm	117mm max
ASPB	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	32mm max
ASPBG	Oțel Zincat	Vopsit Pulbere	Gray	ANSI 61	1.5mm	22mm max
ASPBGSS	Stainless Steel 304	Polished			1.5mm	22mm max
ASPBLG	Oțel Zincat	Vopsit Pulbere	Light Gray	RAL 7035	1.5mm	32mm max
ASPBSS	Stainless Steel 304	Polished			1.5mm	32mm max

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.