

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.



CARACTERÍSTICAS

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

IP 20, in accordance with IEC 60529

EMC Shielding:	Sim
Acabamento:	Anodized; Passivated
Material:	Aluminio
Product Type:	Subrack/Chassis



ESPECIFICAÇÕES

Table 1/2


Número de catálogo	Rack Height	Profundidade (D)	Quantidade por embalagem	For Mounting	Board Depth	Gasket Type
24563-172	3U	235mm	1	Backplane	160mm, 220mm	Textile EMC
24563-173	3U	295mm	1	Backplane	160mm, 220mm, 280mm	Textile EMC
24563-174	3U	355mm	1	Backplane	160mm, 220mm, 280mm	Textile EMC
24563-472	6U	235mm	1	Backplane	160mm, 220mm	Textile EMC
24563-473	6U	295mm	1	Backplane	160mm, 220mm, 280mm	Textile EMC
24563-474	6U	355mm	1	Backplane	160mm, 220mm, 280mm	Textile EMC

Table 2/2

Número de catálogo	Shock and Vibration Tolerance	Inclui alça	Instalação	Em conformidade com	Rack Width	Static Load
24563-172	5g (force)	Não	Rack	IEC 60297-3-103	84HP	15kg
24563-173	5g (force)	Não	Rack	IEC 60297-3-103	84HP	15kg
24563-174	5g (force)	Não	Rack	IEC 60297-3-103	84HP	15kg
24563-472	5g (force)	Não	Rack	IEC 60297-3-103	84HP	15kg
24563-473	5g (force)	Não	Rack	IEC 60297-3-103	84HP	15kg
24563-474	5g (force)	Não	Rack	IEC 60297-3-103	84HP	15kg

DETALHES ADICIONAIS DO PRODUTO

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.