

Front Panel, Front Anodized, Rear Conductive, Unshielded

Front panel, unshielded, front anodized and rear conductive.

CARACTERISTICAS

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive



Profundidade (D): 2.5mm
Material: Alumínio
Acabamento: Anodized; Passivated
Accessory Type: Front panel
Product Type: Front Panel
Tipo: Front Panel without Handle



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Rack Height	Rack Width	Quantidade por embalagem	Instalação	Front Finish	Rear Finish
30847-466	5U	28HP	1	Screw-on Front	Anodized	Conductive
30847-459	2U	42HP	1	Screw-on Front	Anodized	Conductive
30847-462	4U	28HP	1	Screw-on Front	Anodized	Conductive
30847-460	2U	63HP	1	Screw-on Front	Anodized	Conductive
30838-043	3U	4HP	1	Screw-on Front	Anodized	Conductive
30847-458	2U	28HP	1	Screw-on Front	Anodized	Conductive
30847-467	5U	42HP	1	Screw-on Front	Anodized	Conductive
30847-469	5U	84HP	1	Screw-on Front	Anodized	Conductive



Número de catálogo	Rack Height	Rack Width	Quantidade por embalagem	Instalação	Front Finish	Rear Finish
30847-468	5U	63HP	1	Screw-on Front	Anodized	Conductive

Table 2/2						
Número de catálogo	Treated Edges	Em conformidade com	EMC Shielding	Altura (H)	Largura (W)	Certifications
30847-466	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	217.4mm	141.9mm	
30847-459	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	84mm	213mm	
30847-462	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	172.9mm	141.9mm	
30847-460	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	84mm	319.7mm	
30838-043	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4mm	20mm	RoHS
30847-458	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	84mm	141.9mm	
30847-467	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	217.4mm	213mm	
30847-469	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	217.4mm	426.4mm	
30847-468	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	217.4mm	319.7mm	

DETALHES ADICIONAIS DO PRODUTO

Please order fixing material (sleeves, collar screws) separately.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE