

EM-M Conduit/Pipe to Flange Clip



CARACTERÍSTICAS

Supports conduit/pipe or cable from beam flanges

Snap close clip pivots a full 360°

Requires only a hammer to install



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro externo (OD)	Espessura do flange (FT)	Static Load	Certifications
12EM58S1	179820	Stainless Steel 301 (EN 1.4310)		22 - 30 mm	8 - 14 mm	200N	
12EM912S1	179830	Stainless Steel 301 (EN 1.4310)		22 - 30 mm	14 - 20 mm	200N	
16EM1318	173745	Spring Steel	nVent CADDY Armour	23.4 - 35 mm	21 - 28 mm	330N	UL, cUL
16EM24	171740	Spring Steel	nVent CADDY Armour	23.4 - 35 mm	3 - 8 mm	330N	ITB
16EM58	171490	Spring Steel	nVent CADDY Armour	23.4 - 35 mm	8 - 14 mm	330N	ITB


Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro externo (OD)	Espessura do flange (FT)	Static Load	Certifications
16EM912	173570	Spring Steel	nVent CADDY Armour	23.4 - 35 mm	14 - 20 mm	330N	ITB
20EM24	171800	Spring Steel	nVent CADDY Armour	35 - 42 mm	3 - 8 mm	330N	ITB
20EM58	171950	Spring Steel	nVent CADDY Armour	35 - 42 mm	8 - 14 mm	330N	ITB
20EM912	173580	Spring Steel	nVent CADDY Armour	35 - 42 mm	14 - 20 mm	330N	ITB
24EM24	171960	Spring Steel	nVent CADDY Armour	42 - 50 mm	3 - 8 mm	330N	ITB
24EM58	171970	Spring Steel	nVent CADDY Armour	42 - 50 mm	8 - 14 mm	330N	ITB
24EM912	173590	Spring Steel	nVent CADDY Armour	42 - 50 mm	14 - 20 mm	330N	ITB
32EM24	173600	Spring Steel	nVent CADDY Armour	50 - 60 mm	3 - 8 mm	330N	ITB
32EM58	173610	Spring Steel	nVent CADDY Armour	50 - 60 mm	8 - 14 mm	330N	ITB
32EM912	173620	Spring Steel	nVent CADDY Armour	50 - 60 mm	14 - 20 mm	330N	ITB
6EM58	171750	Spring Steel	nVent CADDY Armour	14 - 18 mm	8 - 14 mm	330N	
812EM1318	160075	Spring Steel	nVent CADDY Armour	18 - 30 mm	21 - 28 mm	330N	cUL, UL
812EM24	160120	Spring Steel	nVent CADDY Armour	18 - 30 mm	3 - 8 mm	330N	ITB
812EM58	160130	Spring Steel	nVent CADDY Armour	18 - 30 mm	8 - 14 mm	330N	ITB

812EM912	160140	Spring Steel	nVent CADDY Armour	18 - 30 mm	14 - 20 mm	330N	ITB
----------	--------	--------------	--------------------------	------------	------------	------	-----

Table 2/2

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro externo (OD)	Espessura do flange (FT)	Static Load	Certifications
8EM24S1	179780	Stainless Steel 301 (EN 1.4310)		18 - 22 mm	3 - 8 mm	200N	
8EM58S1	179790	Stainless Steel 301 (EN 1.4310)		18 - 22 mm	8 - 14 mm	200N	
8EM912S1	179800	Stainless Steel 301 (EN 1.4310)		18 - 22 mm	14 - 20 mm	200N	

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

