

Luzes LED para locais perigosos, LEDHL



Hazardous Location LED Strip Lights provide enclosure illumination in hazardous environments. These lights are ideal for remote and darkened enclosure applications in Class 1, Division 2 hazardous areas. With a robust design, these lights have a life span of 100,000 hours and superior lighting performance with easy field angle adjustment brackets. These versatile, light-weight LED lights provide mounting flexibility and are easy to install in an enclosure.

NORMAS DA INDÚSTRIA

UL 844 Listed; File No. E492323

cUL Listed per CSA C22.2 No. 137; File No. E492323

Class I, Division 2 Groups A, B, C, D, T4*; Class II , Division 2,

Groups F, and G, T6; Class III ; Class I, Zone 2, Group IIC ; Zone 22

IEC 60529, IP66/67

*T3C for simultaneous exposure rating, Class I Div. 2 & Class II , Div.

2

CARACTERÍSTICAS

Direct transfer of heat from PCB to the casing to maximize lifetime and reliability

Operating temperature of -40 F (-40 C) to 140 F (60 C)

Easy installation with included mechanical assembly kit while maintaining enclosure rating up to UL Type 4X

Includes 3-ft connect cable with flying leads

Maximum lighting for control panels with 578 to 2,351 lumens and 5,000K color temperature

Linear drive circuit with no flicker or high frequency electronic noise

Easy field angle adjustment with mounting bracket

Wide beam optics with 100 degree angle of illumination

Available in 12, 24, 36, and 48-inch lengths

ESPECIFICAÇÕES

Número de catálogo	Material	Acabamento	Tensão de entrada DC	Current	Light Output
LEDHL24V12	Aluminio	Polido	22 – 28V	0.4A	578lm

Número de catálogo	Material	Acabamento	Tensão de entrada DC	Current	Light Output
LEDHL24V24	Aluminio	Polido	22 – 28V	0.75A	1172lm
LEDHL24V36	Aluminio	Polido	22 – 28V	1.1A	1758lm
LEDHL24V48	Aluminio	Polido	22 – 28V	1.5A	2351lm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE