

Värmare för farliga platser



Designed for hazardous locations where electronic components require protection from cold freezing temperatures, condensation and corrosion.

BRANSCHSTANDARDER

ATEX, IECEx

II2G Ex d IIC T3 / II2 D Ex Td A21 IP65 T200 C

NEC CSA us

Class I, Div 1 Groups A, B, C, D / Class II Div 1 Groups E, F, G

DESIGN

50W, 80W, 200W, 300W, 400W and 600W models available

Provides freeze protection down to -76 F / -60 C

Conductive and Convection heating types available

50W and 80W models can be mounted directly to manifolds, measuring or analyzing instruments, control valves, and similar equipment

200W, 300W, 400W, 600W models are finned heaters that heat the area by transferring the heat from the heater to surrounding air, creating a convection current

Two thermostat options available with a 50 F / 10 C or 68 F / 20 C set point

Material: Aluminium
Yta: Anodiserad
Färg: Svart

SPECIFIKATIONER

Katalognummer	Höjd	Bredd	Djup	Nominell spänning	Uppvärmningskapacitet	Spänning, AC
HLTSTAT10C	28mm	23mm	109mm			
HLTSTAT20C	28mm	23mm	109mm			
DAHHL501AC	89mm	41mm	30mm	115V	50W	110V
DAHHL801AC	89mm	41mm	30mm	115V	80W	110V

Katalognummer	Höjd	Bredd	Djup	Nominell spänning	Uppvärmningskapacitet	Spänning, AC
DAHHL4001A	226mm	229mm	61mm	115V	400W	110V
DAHHL6001A	325mm	229mm	61mm	115V	600W	110V
DAHHL6002A	325mm	229mm	61mm	220V	600W	207V
DAHHL4002A	226mm	229mm	61mm	220V	400W	207V
DAHHL300AC	325mm	229mm	61mm	115V	300W	110V
DAHHL200AC	226mm	229mm	61mm	115V	200W	110V

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE