

Varistar CP Seismic Heavy Load Cabinet, Bellcore Zone 4, EMC, 2100H 600W 600D

KATALOGNUMMER

10630-048



Skåp med IP 55 och EMC-överensstämmelse för extrema seismiska miljöer testade enligt Bellcore zon 4 med en dynamisk bärförmåga på 500 kg. Skräddarsydda lösningar med högre belastning finns tillgängliga. Skåpet används ofta i IKT-applikationer i jordbävningsutsatta områden, bygg- och transportanläggningar, flygplatser, järnvägar och många fler.

Andra dimensioner och versioner kan konfigureras i Onlinekonfiguratorn

DESIGN

Earthquake Secure upp till Bellcore Zone 4, testad med 500 kg per Telcordia GR-63 Core, NEBS certifierad

Statisk last/bärförmåga 1600 kg

Typ av skydd IP55

Hög skärmningskapacitet testad enligt IEC 61587-3, med EN45545-2 brandsäkerhetspackning

PRODUKTATTRIBUT

Produkttyp: Skåp

Produktfamilj: Varistar CP

Rammaterial: Stål

Yta: Pulverlackerad

Rackhöjd: 42U

Höjd: 2000mm

Bredd: 600mm

Djup: 600mm

Statisk belastning: 1600kg

Kapslingsklass: IP55

Uppfyller: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63, kärnzon 4

Färg: Svartgrå

Färgkod: RAL 7021

Frekvens: 50 Hz

Material: Stål

Nettovikt: 180.164kg

Antal i förpackningen: 1

Stöt- och vibrationstolerans: 5g (force)

Fungerar med: Varistar CP

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE