


CPCI System With Pluggable PSU, 4 U, 8 Slot



NÚMERO DE CATÁLOGO

24579-260

4 U CompactPCI System with vertical Card Cage for eight 3U Boards, eight RTM Boards and one 3U Pluggable Power Supply.

CARACTERÍSTICAS

In accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG 2.0 rev. 3.0

System with vertical card cage. Board format Front: 3 U, 160 mm deep; Rear I/O: 3 U, 80 mm deep

Backplane 8 slot, 3 U, 32 bit; system slot right; 8 HP wide CPU can be used; Power backplane

Heat dissipation by 1 U hot-swap fan unit, airflow bottom to top

19"-compatible PSU, 300 W, 3 U, 8 HP

Option to mount a hard disk



CARATERÍSTICAS DO PRODUTO

Product Type: System

Number of Slots: 8

Tipo: 19" Rack Mount

Backplane Type: 3 U CompactPCI

Data Transfer: 32-bit PCI Bus

Power per Slot: 40W

Tensão de entrada AC: 100 – 240V

Airflow Direction: Bottom to Top

Rack Height: 4U

Power Supply Type: (1) Pluggable PSU

Power Supply Included: Sim

Rear I/O: Sim

Em conformidade com: PICMG 2.0 R3.0

Profundidade: 275mm

Altura: 177mm

Net Weight: 11.23kg

Quantidade por embalagem: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALHES ADICIONAIS DO PRODUTO

Modified systems available on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE