


SpectraCool Slim Fit 室内空调 - EMEA



SpectraCool SlimFit Air Conditioners are designed with three space-saving mounting options to maximize footprint. They have been developed to meet the requirements of worldwide industrial customers, easy to specify and easy to use. From filterless operation to global certifications, the SpectraCool Slim Fit Air Conditioner makes automation cooling easy for system designers and operations maintenance teams around the world.

Select units come with a Commboard for Remote Access Control (RAC), an integrated, parametric controller designed to work seamlessly with our enclosure air conditioner units for the purpose of remotely monitoring and managing anywhere from a single unit to an entire network of Spectra cool air conditioners from virtually anywhere in the world with a secure internet connection. Ensure that your systems are always running at optimal temperature levels, increase productivity and improve overall system reliability.

工业标准

UL/cUL 认证 12 型; 文件编号 SA6453

IP 54 内循环, IP 34 外循环

Cooling performance tested by TÜV SÜD Germany, according to DIN EN 14511

IP 54 internal loop, IP 34 external loop

功能

超薄安装设计, 有三个安装选项; 完全嵌入式、部分嵌入式和表面安装

美观设计塑料外壳, 优化气流

R134a 制冷剂

滤网更换简便- 适用于灰尘量极大的环境

配备防尘冷凝器，可以实现无滤网运行

主动冷凝水管理 – 防止滴水

节能旋转压缩机

接线端子电源输入

标准切口尺寸，易于更换

出厂前，每台产品都经过严苛的功能测试

标准空调兼容机柜门开关

附赠安装五金件、密封条和用户手册，使用更方便。

Voltage: 230 V (50/60 Hz), 115 V (50/60 Hz) and 400/460 V 3-phase (50/60 Hz)

Operating temperature range from 50 F / 10 C to 131 F / 55 C

Remote Access Control Units support up to 2 temperature sensors and 10 alarms. They support multiple communication protocols: SNMP, Modbus TCP, Ethernet/IP, and Profinet.

颜色: 浅灰色
完成: 粉末涂层
颜色代码: RAL 7035

技术参数

Table 1/2						
物料号	标称容量 W	标称容量 Btu/h	标称电压	相数	制冷剂	材料
S101016G041	1000W	3400Btu/h	115V	1	R134a	低碳钢
S101026G041	1000W	3400Btu/h	230V	1	R134a	低碳钢
S060526G031	500W	1700Btu/h	230V	1	R134a	低碳钢
S101526G031	1500W	5000Btu/h	230V	1	R134a	低碳钢
S060326G041	300W	1000Btu/h	230V	1	R134a	低碳钢
S101516G041	1500W	5000Btu/h	115V	1	R134a	低碳钢
S101046G031	1000W	3400Btu/h	460V	1	R134a	低碳钢
S101026G031	1000W	3400Btu/h	230V	1	R134a	低碳钢
S162526G041	2500W	8500Btu/h	230V	1	R134a	低碳钢
S162526G031	2500W	8500Btu/h	230V	1	R134a	低碳钢
S101046G041	1000W	3400Btu/h	460V	1	R134a	低碳钢
S060526G041	500W	1700Btu/h	230V	1	R134a	低碳钢
S162026G031	2000W	6800Btu/h	230V	1	R134a	低碳钢
S101016G031	1000W	3400Btu/h	115V	1	R134a	低碳钢

物料号	标称容量 W	标称容量 Btu/h	标称电压	相数	制冷剂	材料
S101526G041	1500W	5000Btu/h	230V	1	R134a	低碳钢
S060326G031	300W	1000Btu/h	230V	1	R134a	低碳钢
S101516G031	1500W	5000Btu/h	115V	1	R134a	低碳钢
S164046G031	4000W	13500Btu/h	460V	3	R134a	低碳钢
S101546G031	1500W	5000Btu/h	460V	3	R134a	低碳钢
S162546G031	2500W	8500Btu/h	460V	3	R134a	低碳钢

Table 2/2						
物料号	标称容量 W	标称容量 Btu/h	标称电压	相数	制冷剂	材料
S101546G041	1500W	5000Btu/h	460V	3	R134a	低碳钢
S162546G041	2500W	8500Btu/h	460V	3	R134a	低碳钢
S164046G041	4000W	13500Btu/h	460V	3	R134a	低碳钢
S162046G031	2000W	6800Btu/h	460V	3	R134a	低碳钢
S162046G041	2000W	6800Btu/h	460V	3	R134a	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合：
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE