

PXI Express 系统，4 U，8 个插槽，Gen2/3

物料号

14579-033



The nVent SCHROFF PXIe 8 Slots System has a 16HP System Slot with 4 Link configuration. 3 of the Hybrid Peripheral Slots are connected by PCIe Gen 3 links with x4 Lanes. The remaining 4 Hybrid Peripheral Slots are connected with PCIe Gen 2 links with 1 lane each.

功能

PXI Express 桌面机箱, 4 U, 44 HP

1 个 PXIe 系统插槽和 7 个混合插槽

四链路系统插槽, 带 PCIe Gen3 x4 的 3 个外设槽和带 PCIe Gen2 x1 链路的 4 个外设槽

强大的散热能力, 风扇噪声低, 支持单插槽 50 W 散热 (假定出风口有 15K 温升)

温控风扇使空气从底部流向背面; 集成式机箱监测模块 (CMM)

宽幅交流输入, 电源开关位于机箱后侧, 电源按钮位于机箱正面 (顶部)

后面板含外部 10 MHz 时钟输入/输出



产品属性

产品类型: 系统

插槽数: 8

类型: 桌面式

背板类型: PXI Express, 4 链路配置

数据传输: PCIe Gen2; PCIe Gen3

每插槽的功率: 50W

交流输入电压: 100 – 240V

气流方向: 从下到后
机架高度: 4U
电源类型: 开放式框架
包含电源: 是
后部 I/O: 否
符合: PXISA PXI-5 R1.1
深度: 315mm
毛重: 15kg
包装数量: 1

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

其他产品详情

系统符合 IEC 60297 - -3 - -101、 - -102、 - -103 标准以及 IEEE 1101.1、1101.10/11 标准；背板，符合 PICMG rev 3.0 和 PXI-5 标准。

可应要求提供定制系统。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE