

EuropacPRO 19" Subrack Kit for Railway, Shielded, SNCF, CompactPCI

Subrack for Railway applications, conform to SNCF Standard, shielded version for CompactPCI applications.



CARACTERISTICAS

SNCF listed, EuropacPRO-fer, tested to NF F 61-005 and NF F 60-002

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

Lateral support bars to NFF standard facilitate insertion of subrack into the (cabinet) frame. The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Static Load:	15kg
Profundidade:	320mm
Material:	Aluminio
Acabamento:	Anodized; Passivated
Em conformidade com:	IEC 60297-3-103; IEEE 1101.10; SNCF NFF 61005; SNCF NFF 60002
Product Type:	Subrack/Chassis
EMC Shielding:	Sim



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Rack Height	Rack Width	Quantidade por embalagem	For Mounting	Board Depth	Gasket Type
21500-046	6U	84HP	1	Backplane	160mm	Textile EMC
21500-047	3U	84HP	1	Backplane	160mm	Textile EMC
21500-072	6U	36HP	1	Backplane	160mm	Textile EMC
21500-069	3U	36HP	1	Backplane	160mm	Textile EMC

Table 2/2

Número de catálogo	Shock and Vibration Tolerance	Inclui alça	Instalação	Certifications
21500-046	5g (force)	Sim	Rack	SNCF, RoHS
21500-047	5g (force)	Sim	Rack	SNCF, RoHS
21500-072	5g (force)	Sim	Rack	RoHS
21500-069	5g (force)	Sim	Rack	RoHS

DETALHES ADICIONAIS DO PRODUTO

Fer = ferroviaire = French Railways, 1 T = 4 HP = 20.32 mm Receptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Version 9 T available on request; Test reports available online.

Guide rails color according to IEEE 1101.10 red = space for CPU-board; grey = space for peripheral boards; green = space for CompactPCI; 19"-power supplies 0,1" offset.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE