


适于背板的 EuropacPro 19 英寸插箱套件, 重型, 屏蔽型

用于安装背板的 EMC 屏蔽型插箱, 重型版本带有 tox 焊接侧板。



功能

带 H 型（“重型”）侧板的插箱, 19 寸法兰固定在侧板上（TOX 冷焊）

提供改造, 如开孔、各种表面或尺寸

扁平包装, 节省空间

铝结构

“重”型水平横梁

用于安装背板的后水平横梁, 带绝缘条

1 GHz 时, EMC 电磁屏蔽约为 40 dB, 2 GHz 时, 约为 30 dB, 前提是正面覆盖屏蔽型前面板, 经测试符合 VG 95373 第 15 部分

内部和外部尺寸符合: IEC 60297-3-100, -101, IEEE 1101.1

抗冲击和振动性能经测试符合德国“Bahn”标准 BN 411002, BN 411003

IP 20, 符合 IEC 60529

EMC 屏蔽: 是
完成: 阳极氧化; 钝化
材料: 铝
产品类型: 插箱/机箱




技术参数

Table 1/2						
物料号	机架高度	深度 (D)	包装数量	用于安装	板深度	垫片类型
24563-172	3U	235mm	1	背板	160mm, 220mm	织物 EMC
24563-173	3U	295mm	1	背板	160mm, 220mm, 280mm	织物 EMC
24563-174	3U	355mm	1	背板	160mm, 220mm, 280mm	织物 EMC
24563-472	6U	235mm	1	背板	160mm, 220mm	织物 EMC
24563-473	6U	295mm	1	背板	160mm, 220mm, 280mm	织物 EMC
24563-474	6U	355mm	1	背板	160mm, 220mm, 280mm	织物 EMC

Table 2/2						
物料号	耐冲击和振动性	包含手柄	安装	符合	机架宽度	静态负载
24563-172	5g (force)	否	机架	IEC 60297-3-103	84HP	15kg
24563-173	5g (force)	否	机架	IEC 60297-3-103	84HP	15kg
24563-174	5g (force)	否	机架	IEC 60297-3-103	84HP	15kg
24563-472	5g (force)	否	机架	IEC 60297-3-103	84HP	15kg
24563-473	5g (force)	否	机架	IEC 60297-3-103	84HP	15kg
24563-474	5g (force)	否	机架	IEC 60297-3-103	84HP	15kg

其他产品详情

支持个性化配置: 支持较大范围高度，宽度和深度定制；根据不同应用可选多种规格导轨,内部附件和安装材料。



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

