


Guide Rail With Coding for CompactPCI/ VME64x, 偏移 0.1"



Plastic offset (0.1") guide rail with coding for CompactPCI and VME64x systems, forms a reliable interface between the subrack mechanics and the sub-assemblies.

可选的键控/编码销可防止板插入到错误的插槽中。导轨还可以通过螺栓固定在水平横梁或 1.5 mm

厚的板上，以满足更高的抗冲击和振动要求。导轨可选配 ESD 夹，用来确保

PCB、把手（IES、IEL）和水平轨道之间的导电接触。适合 RatiopacPRO/-AIR、PropacPRO、CompacPRO 和 EuropacPRO。

功能

偏移 (0.1 英寸) 导轨，带 2 mm

凹槽宽度和编码装置，适用于 CompactPCI 电源

可选 ESD 夹用于 PCB 凹槽，并可用于定位销

可选的编码块防止板插入到错误的槽位置

导轨可以卡入水平横梁（铝挤压件）或 1.5 mm 厚的板中

存储温度：从 -40 °C.. 130 °C



技术参数

物料号	槽宽	颜色	材料	类型	搭配
64560-071	2	绿色	塑料	编码，偏移	插箱, 仪器箱, 机箱
64560-072	2	绿色	塑料	编码，偏移	插箱, 仪器箱, 机箱

其他产品详情

以多个标准包装的形式交货。以单件为单位定价。

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

