

Rail Wallmount SRW, EN50125-3 certified

Railway ready EN50125-3 vibration tested pole-mount stainless steel enclosure for integrated wayside radio, fiber splice, access point and power distribution applications.



CARACTERISTICAS

Finish: powder painting UV resistant

Body: Folded and seam welded 1.5 mm/16 gauge thick stainless steel structure, pre-equipped with M8 blind rivet nuts for wall and pole mounting

Door: Corner formed in one piece, 2 mm/14 gauge stainless steel door with 180° left opening with door stopper. Right opening doors available on request

Roof: Rain & Sun hood to protect against adverse weather conditions

Lock: Swing handle with anti-vibration mechanism equipped with DIN profile half cylinder Ronis 2131A lock and Espagnolette two points locking

Cable access: Gland plate on the bottom. Cut-outs can be requested based on project specific requirements

Protection: Up to NEMA Type 12; NEMA Type 13; NEMA Type 4X; IP66; IK10

Internal accessories: Standard: Document Pocket A4; Optional: 19" uprights on the front, Mounting plate in the rear

External accessories: Optional: Lifting eyes, wall/pole mount kits

Additional information: For outdoor environments, the use of a pressure compensation breather is advised. Also in environments known for quick temperature changes, condensation should be taken into consideration. The standard RWS enclosures are delivered with 2 pressure compensation breathers. One under the hood, one on the Gland plate. The pressure compensation breathers are also IP66.

Right opening doors available on request. Gland plate cutouts can be requested based on project specific requirements.

Optional: 19" uprights on the front, Mounting plate in the rear

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Rack Height	Altura	Largura	Profundidade	Grau de proteção	Cor
SRW0604021	13U	600mm	400mm	210mm	IP66	Light Grey
SRW0606021	13U	600mm	600mm	210mm	IP66	Light Grey
SRW0606030	13U	600mm	600mm	300mm	IP66	Light Grey
SRW0806021	17U	800mm	600mm	210mm	IP66	Light Grey
SRW0806030	17U	800mm	600mm	300mm	IP66	Light Grey

Table 2/2

Número de catálogo	Código de cor	Quantidade por embalagem	Em conformidade com	Acabamento	Frame Material
SRW0604021	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	Pintura electrostática com Acabamento Texturado	Aço inoxidável
SRW0606021	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	Pintura electrostática com Acabamento Texturado	Aço inoxidável
SRW0606030	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	Pintura electrostática com Acabamento Texturado	Aço inoxidável
SRW0806021	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	Pintura electrostática com Acabamento Texturado	Aço inoxidável
SRW0806030	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	Pintura electrostática com Acabamento Texturado	Aço inoxidável

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

