

Modcenter

Automate and precise holes and cutouts machine for Panel Builders. The ModCenter makes your shop more competitive, efficient and improves your bottom line. Reduce your lead times by modifying stocked or quick-ship enclosures on your schedule.



功能

Description: The ModCenter optimizes the machining of enclosures with cut-outs, drill-holes and threaded holes to boost your productivity. The fixation system of the ModCenter allows for placement of one or multiple enclosures, panels and mounting plates in multiple kind of materials. The ModCenter is available in four versions depending on the size of the machinable surfaces and each version is available in a Siemens or Beckhoff control system.

Modern and intuitive Human-machine interface: Easily manage your operations using a large 24" display and a reliable industrial-grade PC with the latest 64-bit operating system. The user-friendly interface makes setup, programming, and day-to-day operations accessible to everyone

Tools: All ModCenters have an automatic tool changing system that accommodates 12 tools and optionally up to 21 tools. The lubrication system extends the lifetime of the tools and is environment friendly as the lubricant is water based.

Fixation: The fixation system has 7 automatic rotary clamps at the bottom and mechanical quick clamps at the top for securing panels and mounting plates. Enclosures are positioned with a synchronized motorized depth adjustment system and are secured with pneumatic fixations pillows allowing for ergonomic and force-free loading of small to large enclosures.

Machinable material: Mild steel, stainless steel, copper, aluminum, PVC, polycarbonate, ABS, GRP and regardless if any of these are powder coated.

Machine software: Ares Commander CAD is an intuitive programming system for the ModCenter available on the console or any other PC in the company network. The software includes a library with enclosures and symbols to

make drawings fast and easily, to be automatically converted to machine code.

Interface: Projects generated with almost all available CAD and E-planning systems in the market can be processed directly on the machine software, using .DXF or .DWG files.

Rated voltage: 400 V, 3~, 50/60 Hz.

Rated current: 32 A.

Compressed air: 6-8 bar, suction capacity 300 l/min.

Machinable panels and mounting plates Width: Up to 2400

Machine footprint Depth: Up to 4500

Control system: ModCenter B - Beckhoff; ModCenter S - Siemens

技术参数

物料号	高度	宽度	材料	完成	颜色	额定电流
MODC163S	1650mm	2400mm	低碳钢	粉末涂层	红色, 灰色	32A
MODC263S	1600mm	2400mm	低碳钢	粉末涂层	红色, 灰色	32A
MODC263B	1600mm	2400mm	低碳钢	粉末涂层	红色, 灰色	32A
MODC280B	2020mm	2400mm	低碳钢	粉末涂层	红色, 灰色	32A
MODC280S	2020mm	2400mm	低碳钢	粉末涂层	红色, 灰色	32A
MODC163B	1650mm	2400mm	低碳钢	粉末涂层	红色, 灰色	32A
MODC293B	2340mm	2400mm	低碳钢	粉末涂层	红色, 灰色	32A
MODC293S	2340mm	2400mm	低碳钢	粉末涂层	红色, 灰色	32A

其他产品详情

Add U at the end of the item no. for UL approved ModCenters.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE