

室内/户外热电冷却器



根据珀尔帖效应进行冷却或加热

Thermoelectric Coolers minimize downtime and component loss by removing heat around critical components within an enclosure. These compact, low-profile coolers using the Peltier effect allow for cooling of small indoor and outdoor enclosures. No condensers, compressors or filters are required making it a reliable solution for demanding low-maintenance environments and low noise.

工业标准

UR, cUR Recognized; Type 12, 3R, 4, 4X; File No. SA6453

CE

IP 65

功能

根据珀尔帖效应进行冷却或加热

不含制冷剂，环保

无过滤设计减少了维护需求

无压缩机空调，适用于苛刻的室内外应用

预接简单的接线端子，方便接线连接

标准包装中包括有护罩和无护罩的型号

半嵌入式安装

低剖面型设计允许垂直和水平安装在任何机柜上，以避免干扰内部元件

Operating temperature range -40 C (-40 F) to 55 C (131 F)

DC Powered operation for 24V and 48V applications

技术参数

物料号	订货号	高度	宽度	深度	标称电压	标称容量 Btu/h
TE162024020	21068	400mm	180mm	184mm	24V	567Btu/h
TE121024011	21072	305mm	157mm	189mm	24V	321Btu/h
TE121048010	21071	305mm	157mm	189mm	48V	321Btu/h
TE121024010	21075	305mm	157mm	189mm	24V	321Btu/h
TE162024010	21077	405mm	187mm	185mm	24V	567Btu/h

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE