

DT1 DIN Rail Surge Protection Class I+II 12.5 kA, 1+0 Mode



CARACTERISTICI

Compact, yet high surge rated pluggable design, using minimum DIN rail width

External back-up fuse is not required up to 315 A (IEC only)

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring



SPECIFICAȚII

Table 1/3

Număr de catalog	DT130010R	DT148010R
Nominal System Voltage (Un)	240 V	400 V
Max Continuous Operating Voltage (Uc)	300 V	480 V
Nominal Discharge Current (In), IEC	20kA 8/20 μs	20kA 8/20 μs
Max Discharge Current (Imax), IEC	50kA 8/20 μs	50kA 8/20 μs
Impulse Current (Iimp)	12.5kA 10/350 μs	10kA 10/350 μs
Voltage Protection Level (Up)	1400V	2000V
Response Time	25 ns Max	25 ns Max
Back-Up Fuse @ Isccr	250 A @ 50 kA 315 A @ 25 kA	250 A @ 50 kA 315 A @ 25 kA
Frequency	50 - 60 Hz	50 - 60 Hz


Număr de catalog	DT130010R	DT148010R
Short Circuit Current Rating (Iscrr)	25kA 50kA	25kA 50kA
Protection Modes	L-PE L-PEN N-PE L-N	L-PE L-PEN N-PE L-N
Temporary Over Voltage 120 min (Ut/mode)	442 V Safe Fail	762 V Safe Fail
Temporary Over Voltage Withstand 5 s (Ut)	337V	571V
Voltage Protection Rating (VPR)	900V	1500V
Nominal Discharge Current (In), UL	20kA 8/20 μs	20kA 8/20 μs
Replacement Module	DT1300M	DT1480M
Short Circuit Current Rating (SCCR)	200kA	200kA
Technology	Thermal Disconnect	Thermal Disconnect
Connection, Solid	35 mm ² Max	35 mm ² Max

Table 2/3

Număr de catalog	DT130010R	DT148010R
Connection, Stranded	25 mm ² Max	25 mm ² Max
Torque (TQ)	4.5 N·m	4.5 N·m
Humidity	5 - 95	5 - 95
Temperature	-35 to 85 °C	-35 to 85 °C
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20	IP 20
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail
Remote Contact Switching Capacity	0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC 1 A @ 125 VAC 1 A @ 250 VAC	0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC 1 A @ 125 VAC 1 A @ 250 VAC
Remote Contacts	Yes	Yes
Status Indication	Mechanical flag	Mechanical flag
Depth (D)	92mm	92mm
Height (H)	90 mm	90 mm
Width (W)	18 mm	18 mm

Număr de catalog	DT130010R	DT148010R
Unit Weight	0.18 kg	0.2 kg
Certification Details	UL® 1449 Edition 5 Type 1CA	UL® 1449 Edition 5 Type 1CA
Complies With	EN 61643-11 Type 1, Type 2 IEC® 61643-11 Class I, Class II	EN 61643-11 Type 1, Type 2 IEC® 61643-11 Class I, Class II

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE