


# Air Baffle, Front Panel, Retrofit Shielding, Steel



The air baffle with flat front panel covers an empty slot and eliminates an air leak. The flat front panel accepts a stainless steel EMC gasket.

## CARACTERISTICI

Air baffle eliminates air leaks from empty slots

Cover is pushed into the guide rail

|                        |                                                                       |
|------------------------|-----------------------------------------------------------------------|
| <b>Finish:</b>         | Anodized; Passivated                                                  |
| <b>Material:</b>       | Aluminiu                                                              |
| <b>Product Family:</b> | EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac |
| <b>Product Type:</b>   | Air Baffle                                                            |
| <b>Type:</b>           | With Front Panel                                                      |



## SPECIFICAȚII

| Număr de catalog | Rack Height | Package Quantity | Depth | EMC Shielding      | Rack Width | Works With      |
|------------------|-------------|------------------|-------|--------------------|------------|-----------------|
| 20848-712        | 3U          | 1                | 160mm | No (Retrofittable) | 4HP        | Subracks, Cases |
| 20848-713        | 3U          | 1                | 220mm | No (Retrofittable) | 4HP        | Subracks, Cases |
| 20848-720        | 6U          | 1                | 160mm | No (Retrofittable) | 4HP        | Subracks, Cases |
| 20848-721        | 6U          | 1                | 220mm | No (Retrofittable) | 4HP        | Subracks, Cases |

## DETALII SUPLIMENTARE DESPRE PRODUS

Air baffle for 280 mm deep and for 80 mm rear I/O boards available on request.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.