

Varistar CP Seismic Heavy Load Cabinet, Bellcore Zone 4, EMC, 2100H 600W 600D

NUMĂR DE CATALOG

10630-048



Cabinet with IP 55 and EMC compliance for extreme seismic environments tested to Bellcore zone 4 with a dynamic load-carrying capacity of 500 kg. Customised solutions with higher loading are available. The cabinet is widely used in ICT applications in earthquake prone areas, Construction and Shipping Facilities, Airports, Railways and many more.

Other dimensions and versions can be configured on the Online Configurator

CARACTERISTICI

Earthquake secure up to Bellcore Zone 4, tested with 500 KGs per Telcordia GR-63 Core, NEBS Certified

Static load-carrying capacity 1600 kg

Type of Protection IP55

High Shielding capability tested per IEC 61587-3, with EN45545-2 Fire safety gasket

ATRIBUTE PRODUS

Rack Height: 42U

Height: 2000mm

Width: 600mm

Depth: 600mm

Frame Color: Black Grey

Frame Color Code: RAL 7021

Cladding Material: Oțel

Cladding Color: Black Grey

Cladding Color Code: RAL 7021

Package Quantity: 1

Complies With: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63 Core Zone 4

Finish: Vopsit Pulbere

Frame Material: Oțel

Static Load: 1600kg

Color: Black Grey

Color Code: RAL 7021

Frequency: 50 Hz

Material: Oțel

Net Weight: 180.164kg

Product Family: Varistar CP

Product Type: Cabinet

Protection Rating: IP55

Shock and Vibration Tolerance: 5g (force)

Works With: Varistar CP

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

