

PXI Express System, 4 U, 18 slots, Gen2

NUMĂR DE CATALOG

14579-043

Desktop PXI Express Chassis for one PXI Express System Controller with up to 16 HP and 7 PXI or PXI Express Boards with 4 HP Width.

CARACTERISTICI

PXI Express Desktop Chassis, 4 U, 84 HP, with handles and 19" mounting brackets

1 PXI Express System Slot with 16 HP width, 1 PXI Express Timing Slot and 16 Hybrid Slots

Gen 2 PCIe switching with a four-link (4x1) System Slot

Powerful cooling concept with low fan noise, 50 W per slot @ 15K temperature increase

Air flow from bottom to rear with temperature controlled fans; Integrated Chassis Monitoring Modul (CMM)

Wide range AC input with mains switch on the rear side, power push button on the front (top) Rear panel external 10 MHz clock inputs/outputs



ATTRIBUTE PRODUS

Product Type: System

Number of Slots: 18

Type: Desktop

Backplane Type: PXI Express, 4 Link Configuration

Data Transfer: PCIe Gen2

Power per Slot: 50W

Input Voltage AC: 100 – 240V

Airflow Direction: Bottom to Rear

Rack Height: 4U

Power Supply Type: Open Frame

Power Supply Included: Yes

Rear I/O: No

Complies With: PXISA PXI-5 R1.1

Depth: 355mm

Gross Weight: 13.1kg

Package Quantity: 1

PXI Express Timing Slot Quantity: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALII SUPLIMENTARE DESPRE PRODUS

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11); Backplane, conforms to PICMG rev. 3.0 and PXI-5

Modified systems available on request

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE