

PXI Express-system, 4 U, 18 kortplatser, Gen3x8



KATALOGNUMMER

14579-042

PXI Express-chassi för en PXI Express-systemstyrenhet med upp till 16 HP och 17 PXI- eller PXI Express-kort med 4 HP bredd.

DESIGN

PXI Express bordschassi, 4 U, 84 HP, med handtag och 19? Monteringsfästen

1 PXI Express-systemplats med 16 hk bredd, 1 PXI Express-tidsfack och 16 hybridfack

Gen 3 PCIe-switchning med en systemkortplats med två länkar (1x16 och 1x8)

Kraftfullt kylningskoncept med lågt fläktljud, 80 W per plats vid 15 K temperaturökning

Luftflöde underifrån och bak med temperaturreglerade fläktar; integrerad chassiövervakningsmodul (CMM)

Bred AC-ingång med huvudströmbrytare på baksidan, strömknapp på framsidan (överst) bakre panel externa 10 MHz klockningångar/utgångar

Trigger in-/utgångsledningar via SMA-kontakten på framsidan

PRODUKTATTRIBUT

Produkttyp: System

Antal fack: 18

Typ: Skrivbord

Bakplanstyp: PXI Express, tvålänskonfiguration

Dataöverföring: PCIe Gen3

Effekt per fack: 80W

Ingångsspänning AC: 100 – 240V

Luftflödesriktning: Underdel till bakdel

Rackhöjd: 4U

Strömförsörjningstyp: (1) PSU som är möjlig att plugga

Strömförsörjning inkluderad: Ja

Bakre I/O: Nej

Uppfyller: PXISA PXI-5 R1.1

Djup: 466mm

Bruttovikt: 10kg

Antal i förpackningen: 1

Antal PXI Express-tidsluckor: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

System i enlighet med IEC 60297-3-101, -102, -103; IEEE 1101,1, 1101,10/11); bakplan, överensstämmer med PICMG rev. 3,0 och PXI-5

Modifierade system finns tillgängliga på begäran

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

