

# CPCI-system för pluggbar PSU, horisontell, 1 U, 2 kortplats

## KATALOGNUMMER

**24579-078**

1 U CompactPCI-system med horisontell korthållare för två 6 U-kort, två RTM-kort och ett CompactPCI 3 U pluggbart nätaggregat.

## DESIGN


I enlighet med IEC 60297 3 101, 102, 103; IEEE 1101,1, 1101,10/11; bakplan i enlighet med PICMG 2,0 rev. 3,0

System med horisontell korthållare. Kortformat framsida: 6 U, 160 mm djup; bakre i/O: 6 U, djup 80 mm

Bakplan (signal- och strömbakplan i en enhet) 2 plats, 6 U, 64 bitar, systemplats vänster, strömkontakt (1 x P 47)

Värmeavledning från fläktar som kan bytas under drift (luftflöde från höger till vänster)

Förberedd för montering av ett 19-tums CompactPCI-nätaggregat (3 U, 8 HP)



## PRODUKTATTRIBUT

Produkttyp: System

Antal fack: 2

Typ: 19 tums rackfäste

Bakplanstyp: 6 U CompactPCI

Dataöverföring: 64-bitars PCI-buss

Effekt per fack: 40W

Ingångsspänning AC: 100 – 240V

Luftflödesriktning: Höger till vänster

Rackhöjd: 1U

Strömförsörjningstyp: (1) PSU som är möjlig att plugga

Strömförsörjning inkluderad: Nej

Bakre I/O: Ja

Uppfyller: PICMG 2.0 R3.0

Djup: 275mm

Höjd: 44.64mm

Bredd: 449mm

Nettovikt: 4.56kg

Antal i förpackningen: 1

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## YTTERLIGARE PRODUKTINFORMATION

Modifierade system finns tillgängliga på begäran.

48 VDC-version på begäran.

## VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

