

# Guide Rail With Coding for CompactPCI/ VME64x, PC, 160 mm, 2 mm Groove Width, 灰色

## 物料号

**64568-090**



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

## 功能

新一代编码型塑料导轨，实现 PCB 或模件盒的可靠固定

稳定性显著提高, 得益于优化设计和高质量材料 (PC)

提高防火安全性能, 符合 EN 45545-2 规范 R22, R23 和 R24 中的最高危险等级 HL3

“无卤素”, 符合 IEC 61249-2-21 标准

导轨可以卡入水平横梁（铝挤压件）或 1.5 mm 厚板中

可以通过螺栓固定到 H 型和 R 型水平横梁，以满足更高的抗冲击和振动要求

可选 ESD 夹，用于 PCB 和水平横梁之间的导电触点

存储温度：从 -40 °C.. 130 °C

产品属性

|                                                                                          |
|------------------------------------------------------------------------------------------|
| 材料: 纤维增强型塑料                                                                              |
| 颜色: 灰色                                                                                   |
| 包装数量: 1                                                                                  |
| 板深度: 160mm                                                                               |
| 槽宽: 2                                                                                    |
| 符合: EN 45545-2                                                                           |
| 产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac |
| 产品类型: 导轨                                                                                 |
| 类型: 编码                                                                                   |
| 搭配: 插箱; 仪器箱; 19" 机箱; 系统                                                                  |
| 毛重: 0.008kg                                                                              |

\*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

其他产品详情

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 销售代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

|                                 |                                      |                                      |                                            |
|---------------------------------|--------------------------------------|--------------------------------------|--------------------------------------------|
| North America                   | Europe                               | Asia                                 | Middle East & Africa                       |
| Locations: 1.703.722.7661       | Staubenhardt, Germany 49.7082.794.0  | Shanghai, China 86.21.2412.6943      | Dubai, United Arab Emirates 971.4.378.1700 |
| Chat with us: nvent.com/schroff | Betschdorf, France +33.3.88.90.64.90 | Qingdao, China +86.532.8771.6101     | Bangalore, India +91.80.6715.2001          |
|                                 | Warsaw, Poland +48.22.209.98.35      | Singapore +65.6768.5800              | Istanbul, Turkey +90.216.250.7374          |
|                                 | Assago, Italy +39.02.932.7141        | Shin-Yokohama, Japan +81.45.476.0271 | Chat with us: nvent.com/schroff            |
|                                 | Chat with us: nvent.com/schroff      | Chat with us: nvent.com/schroff      |                                            |



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE