

带 IEL 把手的面板套件, 屏蔽型, 黑色, 3 U

面板套件, 带 IEL 助拔器黑色把手, 3 U, 前组件。U 型前面板带 EMC 导电布屏蔽条



功能

带 EMC 导电布屏蔽条的 U 型前面板

可承受高达 700 N 的插入力和拔出力 (每对)

可安装微型开关

可根据 IEC 60297-3-103/IEEE 1101.10 标准安装编码键

完成: 阳极氧化; 钝化
材料: 铝
产品类型: 前面板
类型: 带把手的前面板 (PIU)



技术参数

Table 1/2


物料号	机架宽度	包装数量	手柄类型	安装	垫片类型	正面表面处理
20848-585	4HP	1	IEL	正面螺钉安装	织物 EMC	阳极氧化
20848-587	6HP	1	IEL	正面螺钉安装	织物 EMC	阳极氧化
20848-589	8HP	1	IEL	正面螺钉安装	织物 EMC	阳极氧化
20848-590	10HP	1	IEL	正面螺钉安装	织物 EMC	阳极氧化
20848-591	12HP	1	IEL	正面螺钉安装	织物 EMC	阳极氧化

Table 2/2

物料号	反面表面处理	边缘处理	符合	EMC 屏蔽	高度 (H)	机架高度	宽度 (W)
20848-585	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	128.4mm	3U	20mm

物料号	反面表面处理	边缘处理	符合	EMC 屏蔽	高度 (H)	机架高度	宽度 (W)
20848-587	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	128.4m m	3U	30.1m m
20848-589	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	128.4m m	3U	40.3m m
20848-590	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	128.4m m	3U	50.5m m
20848-591	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	128.4m m	3U	60.6m m

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

