


壁挂式碳钢工业机箱，双开门，MAD



The mild steel double door wall mounted enclosure range, MAD, is ideal for installation in confined spaces where a single door, when opened, would take up too much space in front of the enclosure. The doors' loading capacity also increases as it is divided over two doors. With a IP 55 protection degree, components inside the enclosure are well protected and makes it well suited for many different applications.

工业标准

UL 508A Listed; Type 12; File No. E61997

cUL Listed per CSA C22.2 No.0, No.0.4, No.14, No.94; Type 12; File No. E61997

KEMA、GOST、DNV、CE、Lloyds、船级社认证

CSA, File No. 1442951: Type 12

IEC 62208 IP55

CE, UK CA, UL, DNV

功能

Material: Body: 1.5 mm mild steel. Gland plate: 1.4 mm mild steel. Door: 2 mm mild steel Mounting plate: 2 mm galvanized steel / 2.5 mm MAD1001030R5 and above.

Body: Folded and seam welded. Four 8.5 mm diameter holes for wall fixing, pressed out in 20.4 mm diameter × 2 mm depressions, to allow air circulation around the rear part of the enclosure.

Door: Surface mounted with 130° opening. Concealed removable hinges with captive pin. Inner M6 welded studs to mount door profiles MMDP. Two removable mounting profiles on the right hand door and two on the left hand door. Sealing is ensured by an injected one piece polyurethane gasket.

Lock: Customized lock with double-bit for easy opening of the door. Double-bit 3 mm insert and 90° movement. Espagnolette three point locking. Other inserts are available as an accessory.

Mounting plate: The mounting plate is marked vertically at 10 mm intervals, for easy horizontal positioning of equipment. On the top and bottom there are holes to facilitate cable fixing. Fixed onto M8 press welded studs to the rear of the enclosure. All sides, from 800 mm and above, are strengthened by folded edges. By using the AMG accessory, the mounting plate position can be adjusted to any depth.

Gland Plate Opening: Situated at the far rear of the enclosure, to make cabling onto the mounting plate easier.

Protection: IP 55, TYPE 12, IK 10. For outdoor installation, the use of a rain hood, ARF, and 100% polyester paint coating plus corrosion protection primer is recommended. Resistance to corrosion must be taken into consideration for outdoor and indoor applications.

Finish: RAL 7035 structured powder coating.

Delivery: Enclosure with doors and mounting plate (not included for item numbers ending with PER5). Two door mounting profiles on each door. Gland plate(s) with gasket(s), metallic double-bit 3 mm key, and mounting accessories. Earthing facilities.


主体厚度: 1.5mm
门厚: 2mm
颜色: 浅灰色
材料: 低碳钢
完成: 粉末涂层
颜色代码: RAL 7035

技术参数

物料号	订货号	高度 (H)	宽度 (W)	深度 (D)	包含安装板	面板尺寸
MAD1401030R5	MAD1401030R5	1400mm	1000mm	300mm	是	1370 x 950mm
MAD0801230PER5	MAD0801230PER5	800mm	1200mm	300mm	否	
MAD1201230R5	MAD1201230R5	1200mm	1200mm	300mm	是	1170 x 1150mm
MAD1201030PER5	MAD1201030PER5	1200mm	1000mm	300mm	否	
MAD1401030PER5	MAD1401030PER5	1400mm	1000mm	300mm	否	
MAD1201030R5	MAD1201030R5	1200mm	1000mm	300mm	是	1170 x 950mm
MAD0608030PER5	MAD0608030PER5	600mm	800mm	300mm	否	
MAD0801230R5	MAD0801230R5	800mm	1200mm	300mm	是	770 x 1150mm
MAD1001030PER5	MAD1001030PER5	1000mm	1000mm	300mm	否	
MAD0608030R5	MAD0608030R5	600mm	800mm	300mm	是	570 x 750mm
MAD1001030R5	MAD1001030R5	1000mm	1000mm	300mm	是	970 x 950mm
MAD1201230PER5	MAD1201230PER5	1200mm	1200mm	300mm	否	

其他产品详情

* 3 point espagnolette locking.



应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

